

MODCO 24 - 10X10

MODCO MODULAR EXHIBITS

PRODUCT CODE: MODCO24-10x10G



Frame & Graphic



PRODUCT DESCRIPTION

Modco Modular Display 24 is a three-dimensional 10' x 10' pre-designed exhibit booth. Stylish and lively, this booth is built using tool-free perforated modular aluminum frames. Both Modco and a Louver frame are connected using toolless pin connectors. Perforations are completely covered for a flawless finish.

DISPLAY DIMENSIONS	117.375"W X 96.25"H X 17"D	
GRAPHIC SIZES	SIZE	QTY
	40.05"W x 96.25"H	1
	118"W x 96.25"H	2
	40.05"W x 40.05"H	1
	13.2"W x 40.05"H	2
TOTAL		6

GRAPHIC MATERIAL

Stretch Fabric w/ Integrated Block Out

GRAPHIC FINISHING

Silicone beading is sewn around the perimeter of the fabric graphic. Silicone beading is hidden from view once installed.

DISPLAY CONSTRUCTION

Aluminum frame and components

SHIPPING WEIGHTS & DIMENSIONS (FREIGHT ONLY)

Shipping Weight	502lbs
Shipping Dimensions	96"L x 40"W x 15"H

GRAPHIC TURN AROUND TIME

6 business days after proof approval

AVAILABILITY	PFC / MX
--------------	----------

expandbiz

expandbizexhibits.com • Tel: 626-727-3716

PARTS REFERENCE

PARTS LIST



MOD-FRM-992x2418
Qty.4



AF-FTFLT
Qty.2



MOD-FRM-310x992
Qty.2



MOD-FRM-992x992
Qty.1



MOD-FRM-992x2418-LV-BLK
Qty.1



MOD-PNL-CON-LV
Qty.2



MOD-90D-CON
Qty.2



MOD-SM90D-CON
Qty.9



MOD-180D-CON
Qty.4



MOD-PC
Qty.32



MOD-CP-992x2418
Qty.4



MOD-CP-3100 (992mm)
Qty.4



MOD-CTR-DOORS-992X992
Qty.1



MOD-CTR-BM-992x434-WHT
Qty.1



MOD-CC
Qty.20



MOD-CLA-CON
Qty.4

INSTRUCTIONS

1

Name	MODCO 24	Model	
Part No.	MODCO24-10X10G	Location	INDOOR
Location	INDOOR	OC Form	Standard

STEP	QTY	PART NO.	DESCRIPTION
1	4	MSD-1788-20X20-03	Straight Frame, Corner Square Connector, 20/20mm x 20/20mm
2	1	MSD-1788-20X20-01-02-03	L-Bracket Frame, 20/20mm x 20/20mm
3	2	MSD-1788-20X20-01	WP Panel Connector
4	2	MSD-1788-20X20-02	WP Connector
5	1	MSD-1788-20X20-04	L-Bracket WP Connector
6	2	MSD-1788-20X20-05	Adjust. Frame Foot
7	4	MSD-1788-20X20-06	WP Connector
8	4	MSD-1788-20X20-07	Clamp Connector
9	16	MSD-1788-20X20-08	Pin Connector



2

Name	MODCO 24	Model	
Part No.	MODCO24-10X10G	Location	INDOOR
Location	INDOOR	OC Form	Standard

STEP	QTY	PART NO.	DESCRIPTION
1	1	MSD-1788-20X20-09	Adjust. Frame Foot
2	1	MSD-1788-20X20-10	Adjust. Frame Foot
3	1	MSD-1788-20X20-11	Adjust. Frame Foot
4	1	MSD-1788-20X20-12	Adjust. Frame Foot
5	1	MSD-1788-20X20-13	Adjust. Frame Foot
6	1	MSD-1788-20X20-14	Adjust. Frame Foot
7	1	MSD-1788-20X20-15	Adjust. Frame Foot
8	1	MSD-1788-20X20-16	Adjust. Frame Foot
9	1	MSD-1788-20X20-17	Adjust. Frame Foot
10	1	MSD-1788-20X20-18	Adjust. Frame Foot
11	1	MSD-1788-20X20-19	Adjust. Frame Foot
12	1	MSD-1788-20X20-20	Adjust. Frame Foot
13	1	MSD-1788-20X20-21	Adjust. Frame Foot
14	1	MSD-1788-20X20-22	Adjust. Frame Foot
15	1	MSD-1788-20X20-23	Adjust. Frame Foot
16	1	MSD-1788-20X20-24	Adjust. Frame Foot
17	1	MSD-1788-20X20-25	Adjust. Frame Foot
18	1	MSD-1788-20X20-26	Adjust. Frame Foot
19	1	MSD-1788-20X20-27	Adjust. Frame Foot
20	1	MSD-1788-20X20-28	Adjust. Frame Foot
21	1	MSD-1788-20X20-29	Adjust. Frame Foot
22	1	MSD-1788-20X20-30	Adjust. Frame Foot
23	1	MSD-1788-20X20-31	Adjust. Frame Foot
24	1	MSD-1788-20X20-32	Adjust. Frame Foot
25	1	MSD-1788-20X20-33	Adjust. Frame Foot
26	1	MSD-1788-20X20-34	Adjust. Frame Foot
27	1	MSD-1788-20X20-35	Adjust. Frame Foot
28	1	MSD-1788-20X20-36	Adjust. Frame Foot
29	1	MSD-1788-20X20-37	Adjust. Frame Foot
30	1	MSD-1788-20X20-38	Adjust. Frame Foot
31	1	MSD-1788-20X20-39	Adjust. Frame Foot
32	1	MSD-1788-20X20-40	Adjust. Frame Foot
33	1	MSD-1788-20X20-41	Adjust. Frame Foot
34	1	MSD-1788-20X20-42	Adjust. Frame Foot
35	1	MSD-1788-20X20-43	Adjust. Frame Foot
36	1	MSD-1788-20X20-44	Adjust. Frame Foot
37	1	MSD-1788-20X20-45	Adjust. Frame Foot
38	1	MSD-1788-20X20-46	Adjust. Frame Foot
39	1	MSD-1788-20X20-47	Adjust. Frame Foot
40	1	MSD-1788-20X20-48	Adjust. Frame Foot
41	1	MSD-1788-20X20-49	Adjust. Frame Foot
42	1	MSD-1788-20X20-50	Adjust. Frame Foot
43	1	MSD-1788-20X20-51	Adjust. Frame Foot
44	1	MSD-1788-20X20-52	Adjust. Frame Foot
45	1	MSD-1788-20X20-53	Adjust. Frame Foot
46	1	MSD-1788-20X20-54	Adjust. Frame Foot
47	1	MSD-1788-20X20-55	Adjust. Frame Foot
48	1	MSD-1788-20X20-56	Adjust. Frame Foot
49	1	MSD-1788-20X20-57	Adjust. Frame Foot
50	1	MSD-1788-20X20-58	Adjust. Frame Foot
51	1	MSD-1788-20X20-59	Adjust. Frame Foot
52	1	MSD-1788-20X20-60	Adjust. Frame Foot
53	1	MSD-1788-20X20-61	Adjust. Frame Foot
54	1	MSD-1788-20X20-62	Adjust. Frame Foot
55	1	MSD-1788-20X20-63	Adjust. Frame Foot
56	1	MSD-1788-20X20-64	Adjust. Frame Foot
57	1	MSD-1788-20X20-65	Adjust. Frame Foot
58	1	MSD-1788-20X20-66	Adjust. Frame Foot
59	1	MSD-1788-20X20-67	Adjust. Frame Foot
60	1	MSD-1788-20X20-68	Adjust. Frame Foot
61	1	MSD-1788-20X20-69	Adjust. Frame Foot
62	1	MSD-1788-20X20-70	Adjust. Frame Foot
63	1	MSD-1788-20X20-71	Adjust. Frame Foot
64	1	MSD-1788-20X20-72	Adjust. Frame Foot
65	1	MSD-1788-20X20-73	Adjust. Frame Foot
66	1	MSD-1788-20X20-74	Adjust. Frame Foot
67	1	MSD-1788-20X20-75	Adjust. Frame Foot
68	1	MSD-1788-20X20-76	Adjust. Frame Foot
69	1	MSD-1788-20X20-77	Adjust. Frame Foot
70	1	MSD-1788-20X20-78	Adjust. Frame Foot
71	1	MSD-1788-20X20-79	Adjust. Frame Foot
72	1	MSD-1788-20X20-80	Adjust. Frame Foot
73	1	MSD-1788-20X20-81	Adjust. Frame Foot
74	1	MSD-1788-20X20-82	Adjust. Frame Foot
75	1	MSD-1788-20X20-83	Adjust. Frame Foot
76	1	MSD-1788-20X20-84	Adjust. Frame Foot
77	1	MSD-1788-20X20-85	Adjust. Frame Foot
78	1	MSD-1788-20X20-86	Adjust. Frame Foot
79	1	MSD-1788-20X20-87	Adjust. Frame Foot
80	1	MSD-1788-20X20-88	Adjust. Frame Foot
81	1	MSD-1788-20X20-89	Adjust. Frame Foot
82	1	MSD-1788-20X20-90	Adjust. Frame Foot
83	1	MSD-1788-20X20-91	Adjust. Frame Foot
84	1	MSD-1788-20X20-92	Adjust. Frame Foot
85	1	MSD-1788-20X20-93	Adjust. Frame Foot
86	1	MSD-1788-20X20-94	Adjust. Frame Foot
87	1	MSD-1788-20X20-95	Adjust. Frame Foot
88	1	MSD-1788-20X20-96	Adjust. Frame Foot
89	1	MSD-1788-20X20-97	Adjust. Frame Foot
90	1	MSD-1788-20X20-98	Adjust. Frame Foot
91	1	MSD-1788-20X20-99	Adjust. Frame Foot
92	1	MSD-1788-20X20-100	Adjust. Frame Foot

GRAPHIC REFERENCES

GRAPHIC REFERENCE



-  992 x 992 Qty.1
-  310 x 992 Qty.2
-  992 x 2418 Qty.1
-  2976 x 2418 Qty.2

GRAPHIC INSTALL



Place graphic over the front of the frame.



Begin inserting SEG beading at each corner.



Insert the silicone beading with the fabric folded over. The silicone beading should not be exposed.



Using your fingers, push both fabric and silicone beading completely into the extrusion channel.



Continue to push in the remaining silicone beading on each side.



Check the perimeter of the frame for any excess beading that hasn't been pushed in. Graphic should be taut.